


Diverse LAB NMEA connection to Stowe Dataline GX Display

Stowe Dataline GX Display
Set to 'LOAD' or 'FORESTAY'

CALIBRATION
1. With Cal Switch DOWN, set calibration voltage to zero
2. With Cal Switch UP, set CAL VOLTAGE to agree with certificate
3. Set CAL EQUIVALENT figure from certificate into Stowe display
4. Return Cal Switch DOWN for normal function

Zero Coarse Fine



Load Pin
Alternative colours
Black is Blue
Screen is thin Black

Calibration Voltage

12-24 V